



ÜBERSICHT | OVERVIEW

OTOSKOPE | OTOSCOPES

	KaWe EUROLIGHT®										KaWe COMBILIGHT®					KaWe PICCOLIGHT®				
	C10	C30	C30 OP LED/s	C30 VET	C30 VET OP	F.O.30	F.O.30 LED/s	F.O.30	F.O.30	F.O.30 LED/hp	C10	F.O.30	F.O.30 LED/s	F.O.30	F.O.30	F.O.30 LED/hp	C	F.O.	F.O. LED/s	F.O. LED/hp
Versorgungsspannung [V] supply voltage [V]	2,5	2,5	2,5	2,5	2,5	2,5	2,5	3,5	3,5	3,5	2,5	2,5	2,5	3,5	3,5	3,5	2,5	2,5	2,5	2,5
Ladespannung [V] charge voltage [V]									240V						240V					
Stecker plug									EU						EU					
Beleuchtungsart kind of illumination	F.O.																			
	C	•	•		•	•					•						•			
	LED			•																
	F.O. LED standard							•					•						•	
F.O. LED high power									•						•					•
Kopf head	Metallkopf metal head	•	•	•	•	•	•	•	•	•										
	Kunststoffkopf plastic head										•	•	•	•	•	•	•	•	•	•
Verschluss fastening mechanism	Clic-Verschluss click-on connection		•	•	•	•	•	•	•	•		•	•	•	•	•				
	Verschluss mit Schraube connection with fastening screw	•									•									
	Schraubverschluss screw-on connection																•	•	•	•
Griff handle	Metallgriff metal handle	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
	Kunststoffgriff plastic handle																•	•	•	•
Lupe schwenkbar pivoting magnifying glasses	mit 3-facher Vergrößerung with 3-times magnification	•	•			•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
	mit 2,5-facher Vergrößerung with 2.5-times magnification			•																
	mit 2-facher Vergrößerung with 2-times magnification				•	•														
Leuchtmittel illuminant	Xenon-Lampe xenon bulb					•	•	•			•		•	•			•			
	Vakuum-Lampe vacuum bulb	•	•		•	•					•						•			
	LED standard-Lampe LED standard bulb			•			•						•						•	
	LED high power-Lampe LED high-power bulb									•						•			•	
Lebensdauer service life of illuminant	ca. 15 Std. approx. 15 h	•	•		•	•					•						•			
	ca. 20 Std. approx. 20 h						•	•	•			•	•	•				•		
	ca. 50.000 Std. approx. 50,000 h									•						•			•	
	ca. 100.000 Std. approx. 100,000 h			•			•							•					•	
Beleuchtungsstärke illuminance	ca. 7.000 Lux approx. 7,000 Lux	•	•		•	•					•						•			
	ca. 8.000 Lux approx. 8,000 Lux			•			•						•						•	
	ca. 13.000 Lux approx. 13,000 Lux						•					•								
	ca. 15.000 Lux approx. 15,000 Lux							•	•					•	•			•		
	ca. 20.000 Lux approx. 20,000 Lux									•						•			•	
Lichtregler light regulator	stufenlos dimmbar continuously variable dimmer																			
aufladbar in rechargeable in	Ladestation KaWe MedCharge® 4000 (mit KaWe Ladebatterie) KaWe MedCharge® 4000 charging station (with KaWe rechargeable battery)																			
	Steckdose electric outlet																			
mögliche Energiequelle energy source options	Batterie(n) battery (batteries)																			
	KaWe-Ladebatterie KaWe rechargeable battery																			
im Lieferumfang enthalten included items	20 Einweg-Ohrtrichter 20 disposable ear funnels (Ø 2,5/4,0 mm)																			
	3 Dauer-Ohrtrichter 3 reusable ear funnels (Ø 2,5/3,5/4,5 mm)																			
	3 Dauer-Ohrtrichter VET 3 reusable ear funnels (VET) (Ø 4,0/5,0/7,0 mm)																			
	5 Dauer-Ohrtrichter 5 reusable ear funnels (Ø 2,5/3,5/4,5/5,5/9,0 mm)																			
	Ladebatterie 2,5 V rechargeable battery 2.5 V																			
	Ladebatterie 3,5 V rechargeable battery 3.5 V																			
	Reißverschluss tasche bag with zipper																			
	Stofftasche cloth bag																			
erhältlich in available in	night / sky / stone																			